#### T١

# TriSun

## **LIGHT THERAPY & DESK LAMP**



Fact Sheet









Easily alternate between light therapy mode and desk lamp mode, and choose from Daylight 6,000K, Cool light 4,000K and Warm light 2,700K in both settings. This highly functional lamp can be customised to your needs; simply adjust the brightness level to your liking, move the arm and shade into the perfect position, and charge your phone whenever needed using the built-in USB port. With a CRI (Colour Rendering Index) of over 95 and a large 16.5cm diameter shade, you can be sure of an exceptional light quality and shadow-free, evenly diffused light. Ideal for light therapy, office work, reading, creative work, video calls and content creation.

SAD light & desk lamp

10,000 lux at 16cm

Daylight / Cool light / Warm light







## TriSun

## **LIGHT THERAPY & DESK LIGHT**



#### **FEATURES**

- SAD lamp & desk lamp with 3 colour temperature options
- Effortlessly alternate between light therapy mode and desk lamp mode
- Choice of Daylight 6,000K, Cool light 4,000K and Warm light 2,700K in both modes
- Tested to Medical Safety Standard EN/IEC 60601-1
- Light therapy mode: 10,000 lux at 16cm with automatic 30 minute off timer
- Easily adjust the brightness level with the tactile dimmer switch
- Built-in USB port enables convenient charging of your device
- Large 16.5cm [6.5"] diameter shade enables exceptional illumination and spread of light
- Adjustable arm and shade for perfect positioning
- 95+ CRI provides optimum light therapy & ensures accurate colour matching
- · Ideal for light therapy, office work, reading, creative work, video calls, content creation

### **SPECIFICATIONS**

#### **Product information**

Weight 1.4kg Colour Black / Silver Cable length 1.5m

#### Light output

Light source LED 1,000 Lumens 10,000 Lux at 16cm 5,000 Lux at 24cm 2,500 Lux at 36cm 6,000K / 4,000K / 2,700K Colour temperature 95+ Energy consumption 14W

#### **Packaging information**

Height 44.8cm Width 21.2cm Depth 21.2cm Packed weight 1.9kg Products per master carton



